

Vista T R 10


Vista T R 10 910, Vista T R 10 810, Vista T R 10 710, Vista T R 10 610, Vista T R 10 510
10A receiver in canal (RIC) hearing aid series




R 10

Soundscape Manager		910	810	710	610	510
Auto Sound Control	Music	•	•			
	Noise	•	•	•		
	Conversation in a crowd	•	•	•		
	Conversation in a small group	•	•	•		
	Conversation in quiet	•	•	•	•	
	Conversation in noise	•	•	•	•	
	Quiet	•	•	•	•	
	Total environments	7	7	6	3	AutoMic
Speech Target Pro	Speech Target Pro	•	Speech Target2	Speech Target		
	Speech Finder	•	•	•		
	Speech Lock	•				
	Dynamic Sound Mapping	•				
Sound Director	Speech intensifier	•	•	•	•	•
	Noise reduction	•	•	•	•	•
	Adaptive directionality	Multiband	Multiband	Multiband	Multiband	•
Sound Mapping	Sound Mapping	Dynamic	Personalized	•		
	Pinna Effect	•	•	•	•	•
Sound Suite						
	Pulse protector 2	•	•	•	•	•
	Wind control	•	•	•	•	•
	Feedback manager	•	•	•	•	•
	Natural Sound	•	•	•	•	•
Experience innovations						
	Capture All	•	•	•	•	•
	Data logging	•	•	•	•	•
	Upgrade		•	•	•	•
Convenience						
	Wireless synchronization	•	•	•	•	•
	Auto phone	•	•	•	•	•
	Binaural Phone	•	•	•	•	
Fitting						
	Automatic Adaptation Manager	•	•	•	•	•
	Music Equalizer	Binaural	Binaural	•	•	•
	Frequency compression	•	•	•	•	•
	Tinnitus masker	•	•	•	•	•
	IntelliVent	•	•	•	•	•
	Streaming programs	•	•	•	•	•
	Manual programs	•	•	•	•	•
	NAL-NL2/NL1 and DSLv5	•	•	•	•	•
	Fitting channels	20	20	16	10	6

Fitting guides



Standard receiver (xS)



Power receiver (xP)

- Open dome
- ... Closed dome
- - - Power dome or sleeve mold




Vista T R 10 is rated IP 68

Vista TR 10




Standard receiver
(xS)

Power receiver
(xP)

ANSI 3.22 2014/IEC 60118-7 2005 2cc coupler technical data

	Standard receiver (xS)	Power receiver (xP)	
Reference test frequency - IEC 60118-7 (kHz)	1.6	1.6	
	OSPL90		
	Maximum (dB SPL)	111	124
	HFA - OSPL90 (dB SPL)	106	119
	at RTF (dB SPL)	105	121
	Full on gain (input 50 dB SPL)		
	Maximum (dB)	47	57
	HFA - FOG (dB)	40	50
	at RTF (dB)	40	52
	Reference test setting (RTS)		
	Frequency range (Hz)	<100 - 8500	<100 - 7300
	Reference test gain (dB)	29	42
	Current drain at RTS (mA)	1.15	1.25
	Typical battery life (h)	90	80
	Equivalent input noise at RTS (dB SPL)	19	18
	Total harmonic distortion at 500 Hz/800 Hz/1600 Hz (%)	1.0/1.0/1.0	1.5/1.0/0.5
	Electromagnetic compatibility		
	EMC immunity by ANSI c63.19-2011 EMC, omni	M4	M4

IEC 60118-o OES coupler technical data

	Standard receiver (xS)	Power receiver (xP)	
Reference test frequency - IEC 60118-o (kHz)	1.6	1.6	
	OSPL90		
	Maximum (dB SPL)	122	133
	at RTF (dB SPL)	114	130
	Full on gain (input 50 dB SPL)		
	Maximum (dB)	58	67
	at RTF (dB)	48	62
	Basic frequency response		
	Frequency range (DIN 45605) (Hz)	<100 - 9500	<100 - 6700
	Reference test gain (dB)	39	55
	Current drain at RTG (mA)	1.15	1.2
	Typical battery life (h)	90	80
	Equivalent input noise at RTG (dB SPL)	19	19
	Total harmonic distortion at 500 Hz/800 Hz/1600 Hz (%)	1.0/1.5/1.5	1.5/1.5/1.0
	Electromagnetic compatibility		
EMC immunity by IEC 60118-13, 2011 field strength 90/50/35 V/m, omni. IRIL low/medium/high band (dB SPL)	26/24/25	14/16/19	

Legend

- xS receiver
- xP receiver

Test conditions

Battery size: 10; Source: voltage 1.3 V

The measurements obtained with a closed configuration using an HA-1 coupler (ANSI-3.7-1995) or occluded ear simulator (EN 60711, coupling arrangement according to fig. 4 in the test standard). The hearing instrument set to Vista:fit test settings. LLE is applied at an approximate level of 35 dB SPL. Domes should never be fit on patients with perforated eardrums, exposed middle ear cavities, or surgically altered ear canals. In the case of such a condition, we recommend use of a customized earmold. Sound pressure level of these hearing aids exceeds 132 dB SPL.

We reserve the right to change specification data without notice as improvements are introduced.